

Instructions for use

Step 1: Pinch the button and pull the lens out



Step 2: Raise the fully pulled lens



Step 4: Height is not enough, the bottom bracket is supported.



Step 3: Raise the phone cover



It is better to use this product in dark places, please do not use it in backlight or reflective environment (Light refraction can confuse light, blur the picture, and even cause the user to be dizzy)

I.Rigorous design

Easy to carry design , Simple and generous appearance, 8mm lightweight design, booksize feels good when carried.

II:Top quality lens

Acrylic ultra-high-definition Fresnel lens, molded process, more rigorous work, The high-definition effect of the lens is extremely perfect and not easy to break.

III.HD zoom

Zoom on the phone screen by 3-4 times, the picture is clear, the color is vivid, and the 3D visual enjoyment is like theater, no battery power, simple and convenient, energy saving and environment protected, available anytime, anywhere, you personal theater around.

IV.Eye-protected

Use Fresnel lens to reduce radiation and reduce visual fatigue

V.Curved screen design

Enhance the three-dimensionality of the screen with a stylish curved screen design that supports all sizes of mobile phones.

Farther away from the phone, love yourself a little more.