


Tranquil[™] I

OTE TINNITUS NOISE GENERATOR

Device Features:

- Micro OTE case
- #10 battery
- Rotary volume control
- 200 hours battery life
- Micro polytube
- Open-ear dome
- 0 dBSL floor



A mini OTE tinnitus sound generator that offers broad-band white and pink noise.

The Tranquil II OTE utilizes advanced digital signal processing and allows the wearer to select either broadband white noise or broadband pink noise.

Quality Tranquil[™] brand noise generator in a mini case design with micro polytube and popular rotary volume control.

A robust volume wheel controls the Tranquil I which provides easy and accurate adjustment. The device offers a zero noise floor, which can be a critical feature in setting the volume of the device.

The mini ote device employs an ultra-cosmetic case design combined with a micro polytube free-field sound dome which will enable same-day fitting scenarios. The open-ear design of the soft sound dome tip leaves the ear canal open, delivering clean stable sound while allowing the wearer to fully appreciate surrounding sounds in a normal manner. Be sure to specify preference of either broadband general or broadband pink noise when ordering the Tranquil I.

The Tranquil I uses a #10 battery providing 200 hours of typical use.

DEVICE DATA

Both therapy sounds will provide the user with a 0 dBSL noise floor setting.

* Specify preference of White or Pink sound generator at time of Tranquil device order.


WHITE NOISE RESPONSE

Source.....	OFF
Peak.....	77.2 dB SPL
Peak Frequency.....	400 Hz
RMS OUT.....	88.3 dBSPL
Noise Reduction.....	16 dB
Battery Drain.....	0.40 mA
Battery Life (10A).....	200 Hrs.

PINK NOISE RESPONSE

Source.....	OFF
Peak.....	82.7dB SPL
Peak Frequency.....	200 Hz
RMS OUT.....	86.9 dBSPL
Noise Reduction.....	16 dB
Battery Drain.....	0.4 mA
Battery Life (10A).....	200 Hrs.

KEMAR Real-Ear



BLUE CURVE = Broadband white noise
RED CURVE = Broadband pink noise



175 Brookhollow Esplanade
Harahan, LA 70123 504-442-4999
www.softtouchlabs.com



Device Options...

- Tube length: L-M-S sizes available
- Dome size: small is standard, medium or large
- Polytube fitting gauge at www.softtouchlabs.com