

- ADA Compliant
- African Teak Seat

## Product Materials

**FRAME:** 1" dia. 18 gauge stainless steel tubing. Welded.

**WALL BRACKET:** 16 gauge stainless steel with stainless steel piano hinges.

**RETAINING BRACKET:** 16 gauge stainless steel. Positive bullet-type catch holds seat securely in up position.

**SEAT:** 5 hand-rubbed African teak slats, each  $\frac{1}{2}$ " thick and 3" wide with rounded edges.

## Operation

Hinged seat folds up and out of the way when not in use. When properly installed, seat can support up to 250 lbs. – static load.

## Installation

Verify all rough-in dimensions prior to installation. Provide concealed backing or anchors as specified by architect before finished wall is applied. Secure seat support bracket to wall with mounting screws (not included) appropriate for wall construction at holes provided. Locate mounting holes  $16\frac{1}{16}$ " above finished floor. Secure leg support retaining bracket to wall at locations shown.


## Guide Specification

Folding African teak shower seat shall be fabricated of  $\frac{1}{2}$ " thick hand-rubbed African teak slats secured to a stainless steel frame of 1" diameter, 18 gauge tubing. Support leg locks into 16 gauge retaining bracket with bullet-type catch. Shower seat shall meet or exceed ADA guidelines.

**Overall dimensions: 34 $\frac{1}{2}$ "W x 21 $\frac{1}{4}$ "D x 1 $\frac{1}{2}$ " thick.**

## ADA Compliant

- Consult local and national accessibility codes for proper installation guidelines.
- Conformity and compliance to local and national codes is the responsibility of the installer.



**Washroom Accessories**  
Document No. 9030