

## The automatic operator that changes everything


### Beauty, value and versatility are now automatic

When you need a smart solution to improve accessibility the Falcon 8200 Series fits perfectly. Designed for applications like assisted living and ambulatory care, where ease of use is critical, the Falcon automatic operator provides dependable performance at an affordable price point. Everything you need is right in the box, making installation quick and simple. All necessary features are built right in, so configuring the closer is simple and you can easily make more openings more accessible than ever.

### Designed to fit perfectly

The small footprint and elegant design of the Falcon 8200 Series make it a perfect solution for a range of applications.

· Assisted living · Hospitality · Retail · Small office · Restaurants · Ambulatory care





The Falcon 8200 Series automatic operator ensures smooth, convenient door opening for areas requiring easy accessiblity and ADA compliance. This versatile device can also be easily integrated into electrified openings with our wireless accessory offering. Choose the 8231 for pull side or the 8242 for push side installation.

- SmartLatch Senses and overcomes external pressure conditions with a graduated energy assist for secure latching.
- Push 'n' Go Selectable feature allows door to open automatically as soon as it feels pressure.
- Open position learning Automatically sets the opening position and detects obstructions to eliminate wall and door damage.

#### Specifications

Header length	26"
Mounting	Surface mount
Handing	Non-handed
Cycle tested	1 million gear box
Door weight	200 pounds

Consult technical services for use on doors over 200 lbs.

- Pre-load strike assist Removes load on strike lip with a one second delay allowing the door to release and automatically open.
- LED light illumination Light illumination on control box signals accurate installation and helps with connection diagnostics.
- On board power supply (12 VAC) Powers actuators and receivers without the need to install an external power supply,

#### Adjustable features:

Hold-open time delay
Backcheck speed
Backcheck/latch position
Opening/closing speed

### Actuators & accessories



8310-852T shown

#### 6" Round - text with logo

8310-852T	Push plate, wall mount
8310-869F	Mounting box, flush
8310-869S	Mounting box, surface
8310-802	Weather ring



1 1/2" 4 3/4" Jamb - text with logo

8310-818T	Push plate, jamb mount			
8310-819F	Mounting box, flush			
8310-819S	Mounting box, surface			


8310-818T shown




#### Wireless transmitters & receiver


8310-844	Transmitter, wall mount (to be used with 6" round wall mounted actuator)
8310-844J	Transmitter, Jamb mount (to be used with 1 ½" x 4 ¾" jamb actuator)
8310-861	Transmitter, Handheld (single button wireless handheld transmitter)
8310-865	Receiver (wireless receiver with sequencing function)


## 26" Push system







## 26" Pull system






## 26" Drop system (push system only)





# How to order

## 8200 Series



### SC60 Series

STD Standard  DEL Delay (optional, available with SC60/61 only, please specify)  1-5 SC61  Slim SC60-72 (optional, available with SC60/61 only, please specify)  Aluminum  Dark Bronze  Brass*  RW/PA Regular with parallel arm shoe  HW/PA Hold open with parallel arm shoe  HBD Heavy duty arm  DS Dead stop arm  DS/HO Dead stop hold open arm  SS Spring stop arm  SSS/HO Spring stop hold open arm  SC60-30  Blade stop spacer  SC60-61  Auxiliary shoe  SC60-18PA  Plate PA SC60-18PA	2000 201162							
DEL Delay (optional, available with SC60/61 only, please specify)  1-5 SC61  Slim SC60-72 (optional, available with SC60/61 only, please specify)  Aluminum Dark Bronze Brass*  RW/PA Regular with parallel arm shoe HW/PA Hold open with parallel arm shoe HD Heavy duty arm DS Dead stop arm DS/HO Dead stop hold open arm SS Spring stop arm SS/HO Spring stop hold open arm  Soffit shoe support SC60-30  Blade stop spacer SC60-61  Auxiliary shoe SC60-62A Plate SC60-18			Cylinder	Size	Cover	Finish	Arm	Accessories
I-5 SC61  Slim SC60-72 (optional, available with SC60/61 only, please specify)  Aluminum Dark Bronze Brass*  RW/PA Regular with parallel arm shoe HW/PA Hold open with parallel arm shoe HD Heavy duty arm DS Dead stop arm DS/HO Dead stop hold open arm SS Spring stop arm SS/HO Spring stop hold open arm  Soffit shoe support SC60-30 Blade stop spacer SC60-61 Auxiliary shoe SC60-62A Plate SC60-18	STD	Standard						
Slim SC60-72 (optional, available with SC60/61 only, please specify)  Aluminum Dark Bronze Brass*  RW/PA Regular with parallel arm shoe HW/PA Hold open with parallel arm shoe HD Heavy duty arm DS Dead stop arm DS/HO Dead stop hold open arm SS Spring stop arm SS/HO Spring stop hold open arm Soffit shoe support SC60-30 Blade stop spacer SC60-61 Auxillary shoe SC60-62A Plate SC60-18	DEL	Delay (optional, available with SC60/61 only, please specify	<b>()</b>					
Aluminum Dark Bronze Brass*  RW/PA Regular with parallel arm shoe HW/PA Hold open with parallel arm shoe HD Heavy duty arm DS Dead stop arm DS/HO Dead stop hold open arm SS Spring stop arm SS/HO Spring stop hold open arm  Soffit shoe support SC60-30 Blade stop spacer SC60-61 Auxiliary shoe SC60-18	1-5	SC61						
Dark Bronze Brass*  RW/PA Regular with parallel arm shoe HW/PA Hold open with parallel arm shoe HD Heavy duty arm DS Dead stop arm DS/HO Dead stop hold open arm SS Spring stop arm SS/HO Spring stop hold open arm  Soffit shoe support SC60-30  Blade stop spacer SC60-61 Auxiliary shoe SC60-62A Plate SC60-18	Slim	SC60-72 (optional, available with SC60/61 or	nly, please	specify)	)			
RW/PA Regular with parallel arm shoe HW/PA Hold open with parallel arm shoe HD Heavy duty arm DS Dead stop arm DS/HO Dead stop hold open arm SS Spring stop arm SS/HO Spring stop hold open arm Soffit shoe support SC60-30 Blade stop spacer SC60-61 Auxiliary shoe SC60-62A Plate SC60-18	Aluminum							
RW/PA Regular with parallel arm shoe HW/PA Hold open with parallel arm shoe HD Heavy duty arm DS Dead stop arm DS/HO Dead stop hold open arm SS Spring stop arm SS/HO Spring stop hold open arm Soffit shoe support SC60-30 Blade stop spacer SC60-61 Auxiliary shoe SC60-62A Plate SC60-18	Dark Bronze							
HW/PA Hold open with parallel arm shoe HD Heavy duty arm DS Dead stop arm DS/HO Dead stop hold open arm SS Spring stop arm SS/HO Spring stop hold open arm Soffit shoe support SC60-30 Blade stop spacer SC60-61 Auxiliary shoe SC60-62A Plate SC60-18	Brass*							
HD Heavy duty arm  DS Dead stop arm  DS/HO Dead stop hold open arm  SS Spring stop arm  SS/HO Spring stop hold open arm  Soffit shoe support SC60-30  Blade stop spacer SC60-61  Auxiliary shoe SC60-62A  Plate SC60-18	RW/PA	Regular with parallel arm shoe						
DS Dead stop arm DS/HO Dead stop hold open arm SS Spring stop arm SS/HO Spring stop hold open arm  Soffit shoe support SC60-30 Blade stop spacer SC60-61 Auxiliary shoe SC60-62A Plate SC60-18	HW/PA	Hold open with parallel arm shoe						
DS/HO Dead stop hold open arm SS Spring stop arm SS/HO Spring stop hold open arm Soffit shoe support SC60-30 Blade stop spacer SC60-61 Auxiliary shoe SC60-62A Plate SC60-18	HD	Heavy duty arm						
SS Spring stop arm SS/HO Spring stop hold open arm  Soffit shoe support SC60-30 Blade stop spacer SC60-61 Auxiliary shoe SC60-62A Plate SC60-18	DS	Dead stop arm						
SS/HO Spring stop hold open arm  Soffit shoe support SC60-30  Blade stop spacer SC60-61  Auxiliary shoe SC60-62A  Plate SC60-18	DS/HO	Dead stop hold open arm						
Soffit shoe support SC60-30 Blade stop spacer SC60-61 Auxiliary shoe SC60-62A Plate SC60-18	SS	Spring stop arm						
Blade stop spacer SC60-61 Auxiliary shoe SC60-62A Plate SC60-18	SS/HO	Spring stop hold open arm						
Auxiliary shoe SC60-62A Plate SC60-18	Soffit shoe support	SC60-30						
Plate SC60-18	Blade stop spacer	SC60-61						
	Auxiliary shoe	SC60-62A						
Plate PA SC60-18PA	Plate	SC60-18						
	Plate PA	SC60-18PA						

<sup>\*(</sup>Available as an option only, contact customer service at 1-877-671-7011 for more information.)