

PEX-AL-PEX FITTINGS

PRESS FITTINGS FOR PEX-AL-PEX TUBING

MrPEX® Press Fittings for use with MrPEX® ASTM F1281-2005 PEX-AL-PEX tubing in radiant applications. The body is made from DZR brass, double o-rings, and a stainless steel press sleeve. An accurately installed press fitting offers a fast, reliable, and permanent connection.

NOTE: Must use reamer on any PEX-AL-PEX fittings

Press Fitting Assemblies

PART#	TYPE	UNIT
2110500	1/2" PAP to EK 20	Bag of 10
2110625	5/8" PAP to EK 20	Bag of 10



Press Couplings DZR

PART#	TYPE	UNIT
2315050	1/2" PAP to 1/2" PAP	Bag of 10
2216363	5/8" PAP to 5/8" PAP	Bag of 10
2317575	3/4" PAP to 3/4" PAP	Bag of 10
2311010	1" PAP to 1" PAP	Bag of 5



Press Transition to NPT DZR

PART#	TYPE	UNIT
2325050	1/2" PAP to 1/2" NPT	Bag of 10
2325075	1/2" PAP to 3/4" NPT	Bag of 10
2327575	3/4" PAP to 3/4" NPT	Bag of 10
2321010	1" PAP to 1" NPT	Bag of 5



Press Sweat Adapter DZR

PART#	TYPE	UNIT
2355050	1/2" PAP to 1/2" CU	Bag of 10
2355075	1/2" PAP to 3/4" CU	Bag of 10
2357575	3/4" PAP to 3/4" CU	Bag of 10



Press Transition to FIP DZR

PART#	TYPE	UNIT
2335050	1/2" PAP to 1/2" FIP	Bag of 10
2337575	3/4" PAP to 3/4" FIP	Bag of 10

