

# PEXTubing Guidelines

## Maximum Recommended Loop Length

Diameter	Loop Length
5/16"	250'
3/8"	240'
1/2"	300'
5/8"	330'
3/4"	400'

Note: Based on a 10° Delta T

## Maximum Bend Radius

Diameter	Bend Radius
3/8" Nominal Tube Size	3.0"
1/2" Nominal Tube Size	3.75"
5/8" Nominal Tube Size	4.5"
3/4" Nominal Tube Size	5.25"
1" Nominal Tube Size	6.75"

