

# PULSAFEEDER®

The Pulsatron Series MP is a true microprocessor controlled instrument for precise and accurate metering control. Packed with standard features, the Series MP include automatic control via 4-20mA or 20-4 mA inputs, external pace with stop feature and 16 character LCD display with support for English, French, and German languages.

Nineteen distinct models are available, having pressure capabilities to 300 PSIG (21 BAR) @ 3 GPD (0.5 lph), and flow capacities to 504 GPD (79.5 lph) @ 20 PSIG (13 BAR), with a turndown ratio of 1000:1. Metering performance is reproducible to within  $\pm 2\%$  of maximum capacity.

## Features

- Automatic Control, Fully scalable 4-20mA current signal.
- Flow Verification on select sizes.
- Flow Totalization.
- Relay Output for computer interface or AC power.
- Simple Prompts in plain language.
- Available in four languages, English, French, German, and Spanish.
- Alarm Signals for signal loss, full count, circuit failure, pulse overflow and pulse rate high.
- Liquid low-level indicator capability is standard.
- Timed Sequences can be set for selected intervals and rate for repetitive metering.
- Pulse Signals can be multiplied or divided by 1 to 999.
- Flow Rate is displayed as GPH, GPD, or LPH.
- Large easy to read backlit LCD display.

## Controls



### Manual Stroke Rate

- Turn-Down Ratio 100:1

### Stroke Length

- Turn-Down Ratio 10:1

### 4-20mA or 20-4mA Input

- Automatic Control
- Fully Scalable
- Turn-Down Ratio 100:1

### Flow Verification

- Monitors pump output to protect against loss of flow.
- Visual Notification.



## Operating Benefits

- Reliable metering performance.
- Rated "hot" for continuous duty.
- High viscosity capability.
- Leak-free, sealless, liquid end.



## Aftermarket

- KOPkits
- Gauges
- Dampeners
- Pressure Relief Valves
- Tanks
- Pre-Engineered Systems
- Process Controllers (MicroVision)



**PULSAtron® Series MP**  
**Electronic Metering Pumps**

# PULSAtron® Series MP

## Specifications and Model Selection

MODEL	LMK2	LMB2	LMA2	LMD3	LMB3	LMA3	LMK3	LMF4	LMD4	LMB4	LMH4	LMG4	LME4	LMK5	LMH5	LMH6	LMK7	LMH7	LMH8	
Capacity nominal	GPH 0.8	0.21	0.25	0.50	0.50	0.50	0.60	0.85	0.90	1.00	1.70	1.75	1.85	2.50	3.5	5.00	8.00	10.00	200	
Pressure (max.)	PSIG 300	250	50	250	50	100	100	250	50	100	250	50	100	50	50	100	50	35	20	
Connection	Tubing	14" ID X 3/8" OD 3/8" ID X 1/2" OD											3/8" ID X 1/2" OD 1/2" ID X 3/4" OD (LPH8 ONLY) FLOW VERIFICATION (See Note)							
	Piping	14" FNPT											14" FNPT 1/2" FNPT							

Note: Flow Verification: Available on K3, B4 and E4 with connection code JH6, K7 and H7 with connection code H; 14" ID X 3/8" OD only.

### Engineering Data

#### Pump Head Materials Available:

GFPPL  
PVC  
PVDF  
316 SS

#### Diaphragm:

PTFE-faced CSPE-backed

#### Check Valves Materials Available:

##### Seats/O-Rings:

PTFE  
CSPE

##### Balls:

Viton  
Ceramic  
PTFE  
316 SS  
Alloy C

#### Fittings Materials Available:

GFPPL  
PVC  
PVDF

#### Bleed Valve:

Same as fitting and check valve selected, except 316SS

#### Injection Valve & Foot Valve Assy:

Same as fitting and check valve selected

#### Tubing:

Clear PVC  
White PE

Important: Material Code - GFPPL=Glass-filled Polypropylene, PVC=Polyvinyl Chloride, PE=Polyethylene, PVDF=Polyvinylidene Fluoride, CSPE=Generic formulation of Hypalon, a registered trademark of E.I. DuPont Company. Viton is a registered trademark of E.I. DuPont Company. PVC wetted end recommended for sodium hypochlorite.

### Engineering Data

#### Reproducibility:

+/- 2% at maximum capacity

#### Viscosity Max CPS:

For viscosity up to 3000 CPS, select connection size 3, 4, B or C with 316SS ball material. Flow rate will determine connection/ball size. Greater than 3000 CPS require spring loaded ball checks. See Selection Guide for proper connection.

#### Controls:

6-Station Membrane Switch

#### Status Display:

16-Position LCD Dot Matrix Backlight

#### LED Indicator Lights, Panel Mount:

Power On - Green  
Pulsing - Green Flashing  
Stop - Red

#### Stroke Frequency Max SPM:

125

#### External Stroke Frequency Control (Automatic):

4-20 mADC, 20-4 mADC External Pacing

#### Output Relay (Signal Level Option):

24 VDC, 10 mA

#### Output Relay (Power Option):

250 VAC, 50/60 HZ, 0.5A

#### Stroke Frequency Turn-Down Ratio:

100:1

#### Stroke Length Turn-Down Ratio:

10:1

#### Power Input:

115 VAC/50-60 HZ/1 ph  
230 VAC/50-60 HZ/1 ph

#### Average Current Draw:

@ 115 VAC; Amps: 1.0 Amps  
@ 230 VAC; Amps: 0.5 Amps  
Peak Input Power: 300 Watts  
Average Input Power @ Max SPM: 130 Watts


### Custom Engineered Designs Pre-Engineered Systems

Pulsafeeder's Pre-Engineered Systems are designed to provide complete chemical feed solutions for all electronic metering applications. From stand alone simplex pH control applications to full-featured, redundant sodium hypochlorite disinfection metering, these rugged fabricated assemblies offer turn-key simplicity and industrial-grade durability. The UV-stabilized, high-grade HDPE frame offers maximum chemical compatibility and structural rigidity. Each system is factory assembled and hydrostatically tested prior to shipment.

### Dimensions

Series MP Dimensions (inches)																	
Model No.	A	B	B1	C	C1	D	E	Shpg Wt	Model No.	A	B	B1	C	C1	D	E	Shpg Wt
LMA2	5.4	10.3	-	10.8	-	7.5	8.9	13	LMH4	6.2	10.9	-	11.2	-	8.2	9.5	21
LMA3	5.4	10.6	-	10.7	-	7.5	9.2	13	LMH5	6.2	11.3	-	11.2	-	8.2	9.9	21
LMB2	5.4	10.3	-	10.8	-	7.5	8.9	13	LMH6	6.2	11.3	-	11.2	-	8.2	9.9	21
LMB3	5.4	10.6	-	10.7	-	7.5	9.2	13	LMH7	6.1	11.7	-	11.2	-	8.2	10.3	21
LMB4	5.4	10.6	-	10.7	-	7.5	9.2	13	LMH8*	6.1	-	10.9	-	10.6	8.2	-	25
LMD3	5.4	10.6	-	11.2	-	7.5	9.2	15	LMK2	5.4	10.3	-	10.8	-	7.5	8.9	13
LMD4	5.4	10.6	-	11.2	-	7.5	9.2	15	LMK3	5.4	10.6	-	10.7	-	7.5	9.2	13
LME4	5.4	10.6	-	11.2	-	7.5	9.2	15	LMK5	5.4	10.9	-	11.7	-	7.5	9.5	18
LMF4	5.4	10.6	-	11.7	-	7.5	9.2	18	LMK7	6.1	11.7	-	11.2	-	8.2	10.3	21
LMG4	5.4	10.6	-	11.7	-	7.5	9.2	18									

NOTE: Inches X 2.54 = cm / \* the LMH8 is designed without a bleed valve available



27101 Airport Road  
Punta Gorda, FL 33982  
Phone: ++1(941) 575-3800  
Fax: ++1(941) 575-4085

www.pulsatron.com



An ISO 9001 Certified Company

EMP027 B15

