

WT 1

WEIGHING INDICATOR

weightechUSA.com



UNIVERSAL WEIGHING TERMINAL

W&M APPROVED

For industrial use

Directives: 2014/30/EU, 2014/31/EU, 2014/35/EU

Standards: EN 45501, OIML R76-1, EN 61000-6-2, EN 61000-6-3, NAMUR NE21, EN 62368-1, WELMEC 8.8

FC EMI compliance with FCC Part 15

NTEP NTEP approval as indicating element

ETD ETL certified in accordance with UL 62368-1 and CSA C22.2 No. 62368-1
Intertek

IE indicating element

CE EU Type-examination Certificate as non-automatic weighing instrument

Other certificates on demand

Canada Measurement Canada: Approval as indicating element

WT 1

WEIGHING INDICATOR



Stainless steel housing IP69K

Suitable for harsh environment weighing locations. With mounting brackets for desk-top or wall-mount installation. Integrated power supply unit, sealed cable glands for all cable connections.

Keyboard

With function keys for zero setting, taring, printing, totalizing and special functions.

Color display

For indication of weight, multi-lingual operator prompts and calibration dialog. With backlighted, 11 cm (4.3") display.

Power supply

110–240 V AC or 12–30 V DC (integrated) for stationary use or 12–30 V DC (integrated) for mobile use.

Universal Use

Suitable for difficult environmental conditions and locations with high hygienic standards, as in the food, pharmaceutical and chemical industry.

High Operational Security

Fast and error-free operation is ensured by a color display for the indication of weight, IDs and operator prompts.

Weighing Electronics

WT1 connects to one scale with analog strain gauge load cells, entry impedance 43 Ohm–3.3 kOhm (e. g. suitable for 8 x 350 Ohm load cells), or via zener barriers, entry impedance 87.5 Ohm–3.3 kOhm (e. g. suitable for 4 x 350 Ohm load cells), or digital load cells. The weighing terminal provides a W&M approved resolution of up to 10,000 d. Calibration is possible as single or multiple-range (e. g. 3 x 3,000 d) and as single or multi-interval scale.

Weighing Program

Display of net, tare and gross weight. Operator prompting for capturing of weight or piece count. Totalizing is also possible. Plug-on modules are used to set up the IT1 for applications of varying complexity.

Data Logging

Via optional printer interface. The print layout for labels or forms is configurable.

Printout of weights, totals, date, time and consecutive-no.

Data Transmission To PC

Via optional PC interface. Transmission of date, time, consecutive No. and weight after each weighing cycle.

PC ONLINE Mode

Via optional PC interface. Reading of weight, taring, zero setting and other functions can be remotely controlled from a PC.

Weights can be stored in an internal W&M approved data archive for verification. Data transmission is possible through serial interface or Ethernet LAN.

Switching And Filling

With optional input/output modules 3 weight thresholds can be monitored, e. g. for max. or min. values.

Start of weighing cycle and taring is possible from external switches.

Alternatively the inputs and outputs can be used for a filling sequence with start/stop/interrupt and two-speed cut-off.


WT1

WEIGHING INDICATOR

STANDARD PROGRAMS

BASIC

W&M approved weighing terminal
Taring, weighing and totalizing,
printout of ticket.




Desktop or floor scale

Connection to
printer, PC or
remote display

CHECK

Checkweighing terminal
Weight tolerance check with color change
and output signals for 'under tolerance',
'within tolerance' and 'over tolerance'.



Connection to
relay unit or PLC


ONLINE

W&M approved ONLINE weighing terminal
Transmission of weights on request from PC,
via serial interface or Ethernet, internal storage
of 1,000,000 weighings possible in approved data
archive.



WT1

Weighing terminal with setpoints
Min. / max. weight monitoring for hopper scales,
output signals for: 'weight under min.'
and 'weight over max.'




Hopper scale

Connection to
relay unit or PLC

WT1


Mobile weighing
With data logging
(WT1 power supply 12–30 V DC).



Connection to:
printer

PC COM+


PC Software Tool PC COM+ (Option)
ActiveX component for the communication
between Windows programs and WT1
terminals in ONLINE mode. In combination with
PC ARCHIVE option to store weights internally or on PC
hard disk in an approved data archive.



Compatibility:
Windows 7...10

PC ReadIT

PC Software Tool PC ReadIT (Option)
Reception of weighing data and storage
in an ASCII file (*.txt) or a database.
Supported databases: MS SQL, MS ACCESS,
Oracle, Interbase SQL or ODBC.



Compatibility:
Windows 7...10

WT 1

WEIGHING INDICATOR



Construction

Compact stainless steel housing protected to IP69K, for desk-top, wall-mount and column-mount installation or as panel-mount version, suitable for harsh environments, all cable connections through sealed cable glands.

Display and keyboard

Bright 4.3" (11 cm) color screen for indication of weight and operator prompts and calibration.

Sealed membrane keyboard with tactile feedback, with soft keys for zero setting, taring, printing, totalizing and special functions.

Weighing electronics

- Connection to scales with analog strain gauge load cells, entry impedance 43 Ohm–3.3 kOhm (e. g. suitable for 8 x 350 Ohm load cells), or via zener barriers, entry impedance 87.5 Ohm–3.3 kOhm (e. g. suitable for 4 x 350 Ohm load cells), W&M approved resolution up to 10,000 d.

- Internal resolution 524,000 d, update rate 50–800/s, smallest load cell signal 0.33 μ V/e.

- Calibration as single or multiple range scale with 1, 2 or 3 ranges or as multi-interval scale.

- Calibration with test weights or through entry of rated output of load cell(s), option for the linearization of the load curve. Clear operator prompts for all steps of calibration sequence.

- Optional interface modules for digital load cells Flintec RC3D, HBM C16i, Mettler-Toledo TBrick, K...).

Electrical connection

110–240 V AC, 50/60 Hz or 12–30 V DC via integrated power supply unit, or 12–30 V DC for power supply via external battery.

Operating temperature

–10 °C (+14 °F) to +40 °C (+104 °F), 95 % relative humidity, non-condensing.

Further options

Internal W&M approved data archive

To record the latest 1,000,000 weighing results.

PC ScaleView

PC software for the display of weighing data and scale status information.

PC COM+ / PC ARCHIVE

PC software for W&M approved recording of weighing data on a PC hard disk, recording of several years on a hard disk possible.

PC ReadIT

PC software for the reception of weighing data and storage in an ASCII file or a database.

WT CONFIGURATOR

PC software for calibration, backup, configuration of user prompts, and editing of print formats (SIM-NET module required).

Remote display

W&M approved WT1 remote display, selectable RS232, RS485 or Ethernet interface.

Remote diagnostics

Via Ethernet/Internet connection with integrated web server.

Splash and dust cover

Transparent plastic cover to protect display and keyboard.

PANEL-MOUNT INSTALLATION

Stainless steel housing fascia plate protected to IP69K, NEMA 4X



Dimension WxHxD:
285 x 224 x 69 mm
(11.2" x 8.8" x 2.7")

Cutout in panel:
268 x 207 mm
(10.6" x 8.1")

Interface options

One socket for serial or Ethernet interface and one socket for digital I/Os or analog output:

PC interface, selectable Ethernet, RS232 or RS485-4-Draht, configurable as 'data transmission after each weighing cycle' or 'in request mode'.

Printer interface, selectable USB, Ethernet, RS232 or RS485, for the connection of a form or ticket printer, printout configurable via display and keyboard.

Interface for remote display, selectable RS232, RS485 or Ethernet, several protocols configurable.

2 digital inputs and 2 digital outputs

Optoisolated, 24 V DC, outputs for setpoint monitoring or simple filling applications, inputs for start of weighing and taring or start/stop of filling.

Additional digital output

Optoisolated, 24 V DC, for +/- check or setpoint monitoring.

Analog output

0–20 mA, 4–20 mA, 0–10 V or 2–10 V, 15 bit, 32,000 divisions, for analog output of weight.

DESK/WALL VERSION

For desk-top or wall-mount installation. Stainless steel housing, IP69K, NEMA 4X.



Desktop installation

Dimension WxHxD:
168 x 177 x 115 mm
(6.6" x 7.0" x 4.5")



Wall installation

Dimension WxHxD:
168 x 151 x 121 mm
(6.6" x 5.9" x 4.8")