

MODEL: 353200 - REMOTE AUDIO STATION



353200



FEATURES

- Audio LED indicates call tone activation
- Night Tone LED indicates night tone level activation
- 3" speaker for increased tone output
- Cancel button for localized call tone cancellation
- Continuous supervision of station
- Plug-in connectors for easy service
- Bio-seal option to cover buttons and allow for easy disinfecting of the station
- 2-gang adapter plate included

SPECIFICATIONS

Power Required: 250mA at 18V

Weight: 0.40 lbs. (0.18 kg)

Size: **W:** 4.71" (11.96 cm)

H: 4.25" (10.80 cm)

D: 1.68" (4.27 cm)

with adapter plate

W: 5.5" (14.0 cm)

H: 5.0" (12.7 cm)

D: 0.6" (1.5 cm) in back box; 0.5" (1.3cm) off-wall

Housing and Finish: High-impact molded ABS 94VO; light grey faceplate

Controls/Indicators: One (1) Push button for night tone audio level, One (1) Night tone indicator LED, One (1) Audio LED, One (1) Cancel button

Terminations: M-Net plug-on connector, M-Net Non-Audio plug-on connector

Backbox Options: 1 gang, Non-gangable, 3 1/2" deep

DESCRIPTION

The Remote Audio Station features a 3" speaker for increased call tone output where extra nurse call tone output is needed. The call tones are configured by coverage. The night tone button allows users to easily toggle the audio level.

The Remote Audio Station is typically located in areas where call tones are needed. The cancel button allows for local muting of the tone at the station. The Remote Audio station is connected to an associated corridor light or domeless room controller and is continually supervised.

*Architect and Engineer (A&E) Specifications available online at: customerconnection.rauland.com
Specifications subject to change without notice*

©Copyright 2010 Rauland-Borg Corporation Printed in USA Rev 12/2010