

**MODEL: 354012 - STAFF ASSIST STATION**



354012

**FEATURES**

- Extra large back-lit button for easier activation
- Elapsed timer output
- Call-assurance LED
- Cancel button
- Plug-in connectors for easy service
- Continuous supervision of station
- Optional antimicrobial Bio-seal to cover buttons and allow for easy disinfecting of the station

**SPECIFICATIONS**

**Power Required:** 6.3mA @ 18VDC

**Weight:** 0.2 lbs (0.8 kg)

**Size: W:** 3.2" (8.1" (8 cm)

**H:** 4.25" (10.9 cm)

**D:** 0.6" (1.5 cm) in back box: 0.5" (1.3 cm) off-wall

**Housing & Finish:** High-impact molded Cycloloy 2950 UL 94-5VB; light grey faceplate

**Controls/Indicators:** One (1) push button for call actuation, One (1) Call-assurance LED, One (1) Cancel button

**Terminations:** Plug-on connector

**Backbox Requirement:** 1 gang (Non-gangable), 3 1/2" Deep

**DESCRIPTION**

The Staff Assist Station is a call pushbutton station providing the ability to place a staff assist call. Pressing the cancel button cancels the call. This station provides an output for an elapsed timer supporting a momentary or latched contact closure output. Using special buttons, the station can be customized for unique call priorities such as: "Code Pink," "Assist," "Bath," "Help," etc. The button can also be used for staff registration such as: "Nurse in Room", etc. The Staff Assist station is connected to its associated corridor light or Domeless room controller and is continually supervised.

*Architect and Engineer (A&E) Specifications available online at: [customerconnection.rauland.com](http://customerconnection.rauland.com)  
Specifications subject to change without notice*

©Copyright 2008 Rauland-Borg Corporation Printed in USA Rev 08/2008