

**MODEL: 354015 - STAFF ASSIST/CODE STATION**



354015

### FEATURES

- Two (2) call points with Call-Assurance LEDs
- Back-lit pushbuttons for easy activation
- Cancel button
- Continuous supervision of station
- Plug-in connectors for easy service
- Elapsed timer outputs
- Optional antimicrobial Bio-seal to cover buttons and allow for easy disinfecting of the station

### SPECIFICATIONS

**Power Required:** 7.1mA @ 18VDC

**Weight:** 0.2 lbs (0.8 kg)

**Size:** **W:** 3.2" (8.0 cm)

**H:** 4.25" (10.8 cm)

**D:** 0.6" (1.5 cm) in back box: 0.5" (1.3 cm) off-wall

**Housing and Finish:** High-impact molded Cycloy 2950  
UL 94-5VB; light grey faceplate

**Controls/Indicators:** (2) push buttons for call actuation,  
Two (2) Call-assurances LEDs, One (1) Cancel button

**Terminations:** Plug-on connectors

**Backbox Requirement:** 1 gang (Non-gangable), 3 1/2"  
Deep

### DESCRIPTION

The Staff Assist / Code Station is an emergency dual pushbutton station that has the ability to place two (2) unique call priorities from a single station. Using special buttons, the station can be customized for unique call-ins such as: "Code Pink", "Push for Help", etc. The buttons can also be used for staff registration such as: "Nurse in Room", etc. The Cancel button allows for cancellation of the call at the station. This type of station is normally located at a patient room head wall for placing a call for help, staff emergency and/or code call. The station provides outputs for elapsed timer(s) (the associated timer must support either a momentary or latched contact closure input). The Staff Assist / Code Station is connected to its associated corridor light or domeless room controller and is continually supervised. A non-cancelable call will annunciate at the associated console(s) when the

station is removed from the system or a short occurs. The call will detail the location of the station (see Configuration and Installation Manual for more details).

*Architect and Engineer (A&E) Specifications available online at: [customerconnection.rauland.com](http://customerconnection.rauland.com)  
Specifications subject to change without notice*

©Copyright 2008 Rauland-Borg Corporation Printed in USA Rev 08/2008

USA-Mt.Prospect, IL  
Canada  
[www.rauland.com](http://www.rauland.com)

• 800-752-7725  
• 905-607-2335

• Fax 800-217-0977  
• Fax 905-607-3554



**Rauland-Borg Corporation**