

# SF337C Emergency Shower Switch

## IL629 Specification Sheet

Tek-CARE<sup>®</sup> Nurse Call Systems • Rev. 13 - 10/2015

### Features

- UL 1069 Listed
- Waterproof if installed per manufacturer's instructions
- Call-placed indicator
- Call cancel at point of origin
- Attractive, flame-retardant (UL<sup>®</sup> 94V-0) plastic faceplate
- 1.1" (28mm) wide pull-down lever
- Washable TPU plastic pull cord kit is included

### Description

The SF337C Emergency Shower Switch is for any location where activation of an emergency signal is required. The design is such that it may be located anywhere in a shower, bath or tub room, regardless of environmental conditions. The combination of rubber-grommetted mounting screws, rubber mounting gasket, and completely sealed front faceplate make it waterproof (if properly installed). Electronic components are mounted on a circuit board, including an industry-proven reliable reed switch for call initiation. The activating magnet is mounted on the large pull-down lever, which is completely sealed in plastic. The indicator LED is also completely sealed.

Due to the flexibility of its design, the SF337C may be used as a pull cord or as a pull down activated emergency switch. The pull cord supplied may be used for emergency call activation, or if desired, the large 1.1" (28 mm) red pull-down lever may be used. Dome light and system annunciation vary according to the manner in which the SF337C is connected.

### Listings



UL<sup>®</sup> 1069 listed; UL<sup>®</sup> File Number E71599.



**SF337C Emergency Shower Switch**  
(cord not shown)

### Specifications

|                  |                                                                                                                                   |         |            |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------|---------|------------|
| Dimensions:      | Height:                                                                                                                           | 4.5"    | (114.3 mm) |
|                  | Width:                                                                                                                            | 2.8125" | (71.4 mm)  |
|                  | Overall Depth:                                                                                                                    | 1.75"   | (44.4 mm)  |
|                  | Projects Front:                                                                                                                   | 0.71"   | (18 mm)    |
|                  | Projects Rear:                                                                                                                    | 1.04"   | (26.4 mm)  |
| Construction:    | Flame-retardant (UL <sup>®</sup> 94V-0) plastic                                                                                   |         |            |
| Connections:     | Plug-in type.                                                                                                                     |         |            |
| Flush Housing:   | Single-gang ring with square box; for Tek-CARE <sup>®</sup> 500 use plastic single-gang box with minimum 2.875" × 2.125" opening. |         |            |
| Surface Housing: | TekTone <sup>®</sup> IH527 plastic back box for Tek-CARE <sup>®</sup> 500.                                                        |         |            |

### Applicable Systems

Tek-CARE<sup>®</sup>400P5 Nurse Call System  
 Tek-CARE<sup>®</sup>NC300II Nurse Call System  
 Tek-CARE<sup>®</sup> NC200, NC150, NC110 Nurse Call Systems  
 Tek-CARE<sup>®</sup>500 Wireless Emergency Call System