

MODEL: R5K ENHANCED SINGLE PATIENT STATION w DIN



R4K17V



FEATURES

- One (1) DIN receptacle for resident entertainment controls and pillow speaker intercom with entertainment muting during nurse call.
- Interfaces with specialty beds via optional module
- Call-Assurance/ Monitor LED with Cancel button
- Continuous supervision of station
- Single point output for lighting control and radio stepper attachment
- Interface for full lighting control options with additional control module and pillow-speakers
- Optional antimicrobial Bio-seal to cover cancel button and allow for easy disinfecting of the station
- Plug-in connectors for easy service
- Annunciates cord-out

SPECIFICATIONS

Power Required: 22 mA @15 VDC

Power Required when used with Speaker Module:
25 mA @15 VDC

Weight: 0.2 lb. (0.09 kg)

Size: W: 3.2" (8.0 cm)

H: 4.25" (10.8 cm)

D: 0.6" (1.5 cm) in back box: 0.5" (1.3 cm) off-wall

Housing and Finish: High-impact molded Cycloy 2950 UL 94-5VB; light grey faceplate

Controls: One (1) DIN receptacle, One (1) Call-Assurance/ Monitor LED, and One (1) Cancel button

Terminations: Plug-on connectors

Backbox Requirement: 1-gang, (Non-gangable) [W: 2.25" (5.7 cm) H: 4" (10.2 cm) D: 3.5" (8.9 cm)]

Backbox Requirement when used with Speaker

Module: 3-gang, Non-gangable [W: 5.5" (14 cm) H: 3.75" (9.5 cm) D: 3.5" (8.9 cm)]

NOTE: If using lighting control, additional backbox space is required

Certification: Designed for compliance to ANSI/UL 1069, IEC 60950, CE, RoHS / WEEE Compliant. Assembled in a U.S. FDA Registered facility.

DESCRIPTION

The Responder® 5000 Enhanced Single Patient Station w DIN allows both residents and staff to place different call-ins, depending on their requirements, to the assigned nurse console(s), annunciate panel(s), or wireless devices. The station can interface with call cords, entertainment speakers, or specialty beds to initiate calls, control lighting, provide entertainment control, and allow intercom to the console over the optional Responder 5000 Speaker Module. When used with Pillow Speakers, audio capabilities are transferred to the Pillow Speakers. When used with the Responder 5000 Feature Bed Interface module, the

audio capabilities are transferred to the bed rail with entertainment muting and the pillow speakers if used. The addition of the Responder 5000 Single Lighting Control Relay allows for full lighting control options though the buttons on the pillow speaker or CCDIN3 call cord.

The station is connected to its associated corridor lamp or domeless room controller and is continually supervised for station presence. Though programming, a "Trouble" message can annunciate at the associated console(s) when the station is removed from the system.