

ACCUTECH 700169

IS/BR Software | Centralized Wander Management Infrastructure Hub

PRODUCT OVERVIEW

The Accutech 700169 IS/BR Software serves as a core hardware intelligence component within advanced wandering management and resident safety infrastructures. It is engineered to bridge the gap between physical perimeter sensors deployed at facility exits and localized control monitoring stations. By aggregating and processing automated security credentials and high-speed data telemetry from protected boundaries, it eliminates the operational complexity of managing individual entry points. This centralized topology ensures that large-scale senior care, nursing home, memory care, and hospital facilities maintain instantaneous, real-time situational awareness.

Deployed directly between peripheral zone controllers, transmitter wands, door controllers, and central administration computers running management platforms, the 700169 module channels complex wireless and serial data traffic. This proactive routing method eliminates communication bottlenecks and guarantees that complex localized actions—such as authorized staff bypass, secure visitor access, and localized security overrides—are instantly synchronized with perimeter sensors. This active tracking processing ensures absolute protection across expansive hospital wings, long care facility corridors, and high-risk resident zones by establishing an uncompressed, bidirectional data pipeline for system programming, real-time diagnostics, and unified event logging across both IS (IntelliSURV) and BR (Beacon Receiver) configurations.

ARCHITECTS AND ENGINEERS (A&E) SPECIFICATION

- **System Infrastructure:** The contractor shall supply, install, and configure the Accutech 700169 IS/BR Software package to act as the primary configuration and central monitoring interface bridging the peripheral exit network and the central management workstation. The architecture must support bidirectional communication to synchronize active bypass states, tag initialization registries, and real-time controller logs directly with the host computer software.
- **Healthcare Environment Protection:** The data translation software assembly shall incorporate a durable, commercial-grade architectural logic design explicitly engineered to sustain continuous clinical exposure, operating reliably across standard high-traffic healthcare IT environments.
- **Access and Control:** The system's logical data interface shall feature automated data direction control paths to allow authorized clinical staff, security personnel, and system administrators to issue network-wide bypass commands, hardware configuration adjustments, baseline parameter updates, and alarm resets from the central software console.
- **Enclosure and Durability:** The software logic core shall be deployed and protected inside a compact, ruggedized commercial-grade master controller chassis or central administration workstation optimized for clean placement within network hubs.
- **System Interoperability:** The interface architecture must feature validated native compatibility for direct connection with Accutech IS and BR series wander management systems, ensuring non-latent signaling, baseline software handshakes, and credential processing across the facility's dedicated security network.

SYSTEM COMPONENTS

The 700169 IS/BR Software incorporates several fundamental integrated sub-modules and physical connection layouts:

- **High-Speed IS/BR Core Logic Engine:** The primary multi-layer internal computing matrix dedicated to handling automated initialization algorithms, zone sync pathways, and bidirectional network conversion protocols.
- **Industrial System Interconnect Communication Driver:** A ruggedized, low-resistance logical data interface configured to accept hardwired lines and serial diagnostic inputs from the door controller network.
- **Dedicated Data Configuration Port Expansion Layout:** An integrated, high-durability physical port layout designed for a direct, secure connection to local host workstations, programming dongles, or server expansion slots.
- **Transient Voltage & Protocol Encryption Array:** Internal safety logic engineered to isolate delicate computing nodes from communication anomalies, unauthorized data intrusions, and electrostatic discharge (ESD).
- **Vandal-Resistant Infrastructure Enclosure Matrix:** A lightweight, commercial-grade impact-resistant shell providing absolute physical protection for the interior computing circuitry within busy administrative deployment spaces.

FEATURES AND BENEFITS

- **Centralized Boundary Awareness:** Consolidates multiple peripheral controller channels and system parameters down to a single network connection on the administration server, greatly simplifying hardware footprints and reducing response times for clinical teams.
- **Seamless Protocol Conversion:** Automatically translates complex electronic security identifiers, beacon signals, and elopement codes into standard virtual infrastructure layouts without data packet loss or communication delays.
- **Dual-Platform Compatibility:** Provides seamless integration across both IS (IntelliSURV) and BR (Beacon Receiver) hardware environments, allowing facilities to scale and manage diverse regional tracking topologies under a single software interface.
- **Diagnostic Status Indicators:** Features integrated visual configuration paths to provide clear feedback on data transmission, upload verification, and packet reception, streamlining troubleshooting tasks for facility maintenance teams.
- **Validated Platform Interoperability:** Engineered for native plug-and-play compatibility with Accutech security networks and software suites, ensuring a unified approach to facility patient protection.

PRODUCT SPECIFICATION

Manufacturer	Accutech Healthcare Security Solutions
Product Model Name	IS/BR Software
Part Number / SKU	700169

Component Technology Type	Central System Optimization, Monitoring Architecture & Network Data Interface Module
Host Workstation Link	High-Speed Integrated Serial / USB System Communication Interface Loop
Device Interface Port	Dedicated Power Input & Startup Communication Port Layouts
Software Medium Delivery	Secure Pre-Programmed Microchip Module / Physical Logic Drive Package
Input Operating Voltage	12 VDC System Nominal Supply Loop Target
Visual Diagnostic Indicators	Dedicated Feedback Arrays for Power Input and Active Data Transfer Verification
Wander System Compatibility	Accutech ResidentGuard, IS Series, BR Series, and Central Infrastructures
Chassis Construction	High-Impact, Commercial-Grade Structural Thermoplastic / Composite Shell
Primary Target Environments	Central IT Server Closets, Technical Terminals, Main Administration Desks

COMPLIANCE AND CERTIFICATION

- **FCC Status:** Designed and certified to meet FCC regulations regarding digital device shielding. This guarantees that internal motor microprocessors, switching pathways, and high-speed data translation steps do not introduce or sustain harmful electromagnetic interference across nearby diagnostic clinical devices or patient networks.
- **UL Listing:** Developed and engineered using interior assembly components compliant with UL safety classifications for low-voltage access control locking mechanisms, information technology equipment, and auxiliary healthcare resident safety tools.
- **RoHS Compliance:** Formulated in alignment with environmental protection directives, ensuring that the internal circuit layouts, external terminal components, and housing finishes strictly restrict the use of lead, mercury, polybrominated biphenyls, and other hazardous materials.