

ACCUTECH 950001-ID

LC Startup Kit | Central Security Infrastructure & Wander Management System Initialization Suite

PRODUCT OVERVIEW

The Accutech 950001-ID LC Startup Kit serves as a core hardware intelligence component within advanced wandering management and resident safety infrastructures. It is engineered to bridge the gap between physical perimeter sensors deployed at facility exits and localized control monitoring stations. By aggregating and processing automated security credentials and high-speed data telemetry from localized door controllers and entryways across a newly established or localized facility deployment, it eliminates the operational complexity of managing individual entry points. This centralized topology ensures that small to medium-scale senior care, nursing home, memory care, and hospital facilities maintain instantaneous, real-time situational awareness during initial system installations, system testing, and baseline deployment setups.

Deployed directly between peripheral zone controllers, transmitter wands, door controllers, and central administration frameworks, the 950001-ID module channels complex serial data traffic. This proactive routing method eliminates communication bottlenecks and guarantees that complex localized actions—such as authorized staff bypass, secure visitor access, and localized security overrides—are instantly synchronized with perimeter sensors. This active tracking processing ensures absolute protection across localized hospital wings, dedicated care facility corridors, and high-risk resident zones by establishing an uncompressed, bidirectional data pipeline for system programming, real-time diagnostics, and unified event logging while driving a visual zone matrix to map multi-door elopement alerts across distinct facility points.

ARCHITECTS AND ENGINEERS (A&E) SPECIFICATION

- **System Infrastructure:** The contractor shall supply, install, and configure the Accutech 950001-ID LC Startup Kit to act as the primary visual status and monitoring interface bridging the peripheral exit networks and the main nurse workstation location. The hardware must support bidirectional communication to synchronize active bypass states, zone alarms, and real-time controller logs directly with the host computer software.
- **Healthcare Environment Protection:** The multi-zone indicator display assembly shall incorporate a durable, commercial-grade structural design explicitly engineered to sustain continuous clinical exposure, operating reliably across standard high-traffic healthcare IT environments.
- **Access and Control:** The device's physical data interface shall feature automated data direction control paths to allow authorized clinical staff, security personnel, and system administrators to issue network-wide bypass commands, hardware configuration adjustments, and alarm resets from the central software console.
- **Enclosure and Durability:** The graphic indicator assembly shall be protected inside a compact, ruggedized commercial-grade enclosure case optimized for clean surface or flush wall mounting directly within administrative spaces, reception corridors, or command hubs.
- **System Interoperability:** The panel display architecture must feature validated native compatibility for direct connection with Accutech wander management systems, ensuring non-latent zone signaling and localized alarm tracking across the facility's dedicated security network.

SYSTEM COMPONENTS

The 950001-ID LC Startup Kit incorporates several fundamental integrated sub-modules and physical connection layouts:

- **672008 ID-TAD System Component:** A specialized system ID tuning and activation device engineered to initialize boundary frequencies, handle automated zone configuration, and synchronize system parameters.
- **680018 Test Tag Assembly (Red):** A dedicated, visible diagnostic verification transponder built for staff execution loops to test physical entry fields safely.
- **100901 Clinical Wearable Bands (Grey):** High-tensile, comfortable patient ankle and wrist attachments engineered to securely anchor electronic protection sensors to monitored residents.
- **200499 Hex Security Bit Hardware:** Specialized mechanical security bit required for professional enclosure enclosure configuration, preventing intentional tampering from unauthorized entities.
- **Unified Documentation & Media Deployment Pack:** Includes part numbers 850000 (Documentation CD), 850001 (Printed Manual Layouts), and 979999 (Technical System Marker) for comprehensive configuration tracing.

FEATURES AND BENEFITS

- **Turnkey Startup Infrastructure Deployment:** Consolidates independent peripheral zone controller channels down to a single visual interface panel connection on the administration server, providing an all-in-one out-of-the-box system foundation for new installations.
- **Elimination of Common Installation Errors:** Dramatically reduces deployment risks and mitigates downstream false alarms by supplying a completely matched set of testing, alignment, and physical installation modules.
- **Seamless Protocol Conversion:** Automatically translates complex electronic security identifiers and exit triggers into an immediate localized virtual mapping layout without data packet loss or communication delays.
- **At-A-Glance Situational Mapping:** Provides immediate physical verification of active elopement risks or door violations across local wings, allowing teams to route response paths to exact exit boundaries.
- **Diagnostic Status Indicators:** Features integrated board-level test parameters to provide clear visual feedback on data transmission, loop power presence, and LED integrity, streamlining troubleshooting tasks for facility maintenance teams.
- **Validated Platform Interoperability:** Engineered for native plug-and-play compatibility with Accutech LC1400 Series security networks and software suites, ensuring a unified approach to facility patient protection.

PRODUCT SPECIFICATION

Manufacturer	Accutech Healthcare Security Solutions
Product Model Name	LC Startup Kit
Part Number / SKU	950001-ID
Component Technology Type	Central Multi-Zone Visual Status Monitoring Interface & Mapping Panel
Included Core Hardware	ID-TAD (672008), Test Tag (680018), Wearable Bands (100901), Security Bit (200499)

Monitored Zone Capacity

Expandable Independent Entry / Exit Points

Device Interface Port

Heavy-Duty Industrial Mechanical Screw Terminal Connection Blocks

Host Workstation Link

High-Speed Integrated Serial Communication Interface / Data Loop

Wander System Compatibility

Accutech ResidentGuard LC Series, Custom Zone Networks, and Central Infrastructure Hardware

Chassis Enclosure Type

Surface or Flush-Mount Rugged Architectural Wall Cabinet Assembly

Primary Target Environments

Main Nurse Stations, Reception Areas, Central Security Rooms, Corridor Hubs

COMPLIANCE AND CERTIFICATION

- **FCC Status:** Designed and certified to meet FCC regulations regarding digital device shielding. This guarantees that internal motor microprocessors, switching pathways, and high-speed data translation steps do not introduce or sustain harmful electromagnetic interference across nearby diagnostic clinical devices or patient networks.
- **UL Listing:** Developed and engineered using interior assembly components compliant with UL safety classifications for low-voltage access control locking mechanisms, information technology equipment, and auxiliary healthcare resident safety tools.
- **RoHS Compliance:** Formulated in alignment with environmental protection directives, ensuring that the internal circuit layouts, external terminal components, and housing finishes strictly restrict the use of lead, mercury, polybrominated biphenyls, and other hazardous materials.